


G10N-40



This classy 10" is a true 'modern vintage' guitar speaker, that delivers an exceptionally well balanced tone that has real Celestion pedigree. The G10N-40 is characterised by satisfyingly deep lows that are complemented by sweet and clear upper mids and an articulate, well-defined top end. Loaded into small combos, the G10N-40 articulates a detailed and warm clean sound, and its balanced response means this versatile speaker is still able to deliver true British grind when pushed to the limit.

8 Frequency Response



General Specifications

Nominal diameter	10", 254mm
Power rating	40Wrms
Nominal impedance	Available 8 or 16
Sensitivity	95dB
Chassis type	Pressed steel
Voice coil diameter	1.75", 44.5mm
Voice coil material	Round copper
Magnet type	Ceramic
Magnet weight	20oz
Frequency range	95-5500Hz
Resonance frequency, Fs	98Hz
DC resistance, Re	Available 6.4 or 12.05

Mounting Information

Cut-out diameter	9.0", 229mm
Diameter	10", 124mm
Magnet structure diameter	4.9", 124mm
Mounting slot dimensions	0.25 x 0.43", 6.5 x 11 mm
Mounting slot PCD	9.6", 245mm
Number of mounting slots	8
Overall depth	4.0", 102mm
Unit weight	3.6lb, 1.6kg