

0 600 8B3 170 – UniversalChainPole 18

Material number	0 600 8B3 170
EAN	3165140888134
Voltage	230 V
Package (D/W/H)	195 x 160 x 1170 mm
1 battery pack PBA 18V 2.5Ah W-B	✓
Charger AL 1830 CV	✓



Technical data

Technical data

Battery type	Lithium-ion
Compatible battery type	Lithium-ion
Battery voltage	18 V
Compatible battery voltage	18 V
Battery charge time	60 h
Oil tank	60 ml
Chain bar length	20 cm
Chain speed	4 m/s
Drive link thickness	1.1 mm
Weight (including chain, bar and battery)	3,6 kg
Weight (including chain and bar)	3,3 kg
Height adjustment	210 – 260
Cutting length	150 cm
Pivoting Head	120 °



Functions

Automatic lubrication	✓
Tip protector	✓

Noise/vibration information (AKE 1)

Sound pressure level	78 dB(A)
Sound power level	92 dB(A)
Uncertainty K	2 dB

Sales information

Positioning

- Ideal for pruning of hard to reach branches

User benefit

- Effortless pruning of tree branches at the ground level without using a ladder thanks to the telescopic pole and pivoting head
- Continuous cutting performance without damaging trees
- Ergonomic, well balanced and lightweight with less strain on arms and shoulders

Highlights

- One battery for all DIY and garden tools in the 18 volt Power4All lithium-ion cordless system
- Syneon Chip – Intelligently controlled energy for every project
- Tip protector and bumper spike for better control on what you cut and undercut
- Oil level indicator and automatic chain lubrication preventing pruner from running dry