

0 600 8A7 F70 – EasyAquatak 110

Material number	0 600 8A7 F70
EAN	3165140935692
Voltage	240 V
Package (D/W/H)	200 x 400 x 375 mm
3 m high-pressure hose	✓
Bosch high-pressure gun	✓
High pressure detergent nozzle, 450 ml	✓
Lance	✓
Rotary nozzle	✓
Variable fan jet nozzle	✓
Water filter	✓



Technical data

Technical data

Motor power	1.300 W
Max. pressure	110 bar
Max. flow rate	330 l/h
Max. flow temperature	40 °C
Self priming capability	0.5 m
Detergent system	High pressure foam
Motor type	Series
Pump type	3 cylinder
Pump material	all metal
Cable length	5 m
Hose length	3 m (PVC)
Weight (without accessories)	3,8 kg
Lances	Lance
Nozzles	Rotary nozzle
Hose reel	Manual

Functions

Compact	✓
Ready to use out of the box	✓
Storage for all accessories/hose/cables	✓
Simple, quick connect fittings	✓
Safe in-use gun storage	✓

0 600 8A7 F70 – EasyAquatak 110

Self priming/use with water tanks	✓
Water filter	✓
All metal pump	✓
Auto-stop system	✓
High pressure foam system	✓

Mobility

Weight of machine	3.8 kg
-------------------	--------

Hose

Hose length	3 m
Hose type	PVC
High pressure hose reel	no

Noise/vibration information

Sound pressure level	85 dB(A)
Sound power level	98 dB(A)
Uncertainty K	3 dB

Sales information

Positioning

- Compact and quick producing effortless cleaning performance

User benefit

- Highly efficient motor pump producing quick and effortless cleaning performance
- Compact, portable design with a broad base for extra stability and storage for all accessories
- Simple push fit connections for quick and easy set up

Highlights

- Includes variable power and rotary nozzles for deeper cleaning
- The high-pressure detergent nozzle reduces cleaning time by quickly applying the soap
- Ready to use out of the box so no customer assembly required

