

PV® 12M



OVERVIEW

Make your vocals really cut through! Rated at 500 watts program and 1,000 watts peak power handling capability, the rugged, trapezoidal PV 12M is built to withstand the rigors of the road. The PV 12M can be angled at either 30 or 45 degrees from the floor in addition to being pole mounted. This two-way system features a 12" Sheffield® Pro 1200+™ premium woofer and a 14T™ 1.4-inch titanium-diaphragm compression driver (no piezos) coupled to a constant-directivity horn with our exclusive Sound Guard™ IV high-frequency driver protection. Two 1/4-inch, full-range parallel inputs allow easy daisy chaining. Top quality performance from a very affordable, low-profile stage monitor!

FEATURES

- Two-way floor monitor
- 68 Hz to 17 kHz
- 12" Sheffield Pro 1200+ woofer w/ 2.5" voice coil
- 14T compression driver w/ titanium diaphragm
- 500 W program power handling
- Sound Guard IV tweeter protection
- carpet covering
- steel handle
- Heavy duty metal grille
- die-cast aluminum pole mount
- 90 x 40 CD horn
- Weight Unpacked: 37.50 lb(17.01 kg)
- Weight Packed: 44.00 lb(19.958 kg)
- Width Packed: 19.25"(48.895 cm)
- Height Packed: 24"(60.96 cm)
- Depth Packed: 14.5"(36.83 cm)