

# PVX™ 12



## OVERVIEW

The PVX 12 passive loudspeakers deliver superior sound quality by utilizing advanced materials like its lightweight, roadworthy molded polypropylene exterior. Lightweight, durable and voiced for live music or speech applications, these two-way speaker systems will handle 400 watts program and 800 watts peak power and feature heavy-duty woofers, 2-3/8" voice coils and the Peavey RX14™ 1.4-" titanium diaphragm compression driver coupled to a constant directivity horn.

## FEATURES

- 400 watts program
- 800 watts peak
- Top, bottom and right side flying point inserts
- Full-coverage heavy-duty perforated steel grille, with powder-coat finish
- Rugged Construction
- Patented, asymmetrical Quadratic Throat
- Waveguide™ Technology - 100° by 50° coverage. 15° upward and 35° downward directing sound to your audience
- RX14™ - Titanium Compression Driver
- Weight Unpacked: 37.00 lb(16.783 kg)
- Weight Packed: 43.00 lb(19.505 kg)
- Width Packed: 20"(50.8 cm)
- Height Packed: 26.75"(67.945 cm)
- Depth Packed: 18.25"(46.355 cm)