

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **5600230548**
Status: **Active**
Overview: Mini50 Connection Systems
Description: CTX50 Receptacle Terminal, Unsealed, Gold Plating, L-Grip, D-Wind, Left Payoff

Documents:

Drawing (PDF)	Application Specification AS-560023-001-CH-001 (PDF)
Product Specification 5600230001-PS (PDF)	Application Specification AS-560023-001-FR-001 (PDF)
Product Specification TS-560023-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-560023-001-001 (PDF)	Product Literature (PDF)

General

Product Family	Crimp Terminals
Series	560023
Application	Power
Crimp Quality Equipment	Yes
Overview	<u>Mini50 Connection Systems</u>
Product Literature Order No	987650-5442
Product Name	CTX50
UPC	889056777698

Physical

Gender	Female
Grip Code	L
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	0.079/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.10-1.40mm
Wire Size AWG	N/A
Wire Size mm ²	0.35


Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	14V DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-560023-001-001, AS-560023-001-CH-001, AS-560023-001-FR-001
Product Specification	5600230001-PS, TS-560023-001-001
Sales Drawing	SD-560023-002-000



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2018 (15
January 2018)

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[560023 Series](#)

Use With

Mini50 Unsealed Single Row Receptacle [34791](#) , Mini50 Unsealed Dual Row Receptacle [34824](#)