



Case Material: Machined aluminum alloy case. Type II MIL-Spec anodized finish

Dims/Weight: Length: 14.6 in. (371 mm) Body Diameter: 0.60 in. (15 mm)
 2.70 oz (76.5 grams) with batteries (included with purchase)

Light Source: C4® LED technology, impervious to shock with a 30,000 hour lifetime

On/Off: Push button tail switch

Battery: Two "AAA" alkaline batteries (included)

- Features:
- C4® LED technology for extreme brightness
 - Eight-inch (20.32 cm) flexible polyethylene-coated extension cable allows for 14" (35.56 cm) of reach
 - IPX4 rated for water resistant operation. All openings o-ring sealed
 - 1 meter impact resistance tested
 - Removable pocket clip
 - Magnetic clip - mount in virtually any position for hands-free use
 - Tail clip stows cable folding light to about the size of a marker; conveniently fits in shirt pocket

Approvals: Most models meet applicable European Community Directives.

Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Item		UPC	Part#
Stylus Pro Reach	Black with White LED	080926-66418-0	66418

Made in China