

Overview

Model Name	APC Essential SurgeArrest PE6U2, 6 Outlets, 2 USB charging ports,120V
Includes	User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Antigua And Barbuda , Argentina , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Canada , Cayman Islands , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Grenada , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , SAINT KITTS AND-NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Trinidad And-Tobago , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Number of Outlets	6
Receptacle Style	NEMA 5-15R

Input

Nominal Input Voltage	120V
Input Power	0 W
Input Frequency	50/60 Hz
Input Connections	NEMA 5-15P
Maximum Line Current per phase	15.0 A
Cord Length	1.83 meters
Maximum Input Current	15 A

Surge Protection and Filtering

Surge energy rating	1080 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	40.0 dB
Peak Current Normal Mode	24 kA
Peak Current Common Mode	48.0 kA
NM Surge Response Time (ns)	1.0 NS
Let Through Voltage Rating	500

Physical

Net Weight	0.54 kg
Maximum Height	30.0 mm
Maximum Width	52.0 mm
Maximum Depth	348.0 mm
Shipping Weight	0.64 kg
Shipping Height	40.0 mm
Shipping Width	115.0 mm
Shipping Depth	380.0 mm
Master Carton Units	6.0

Master Carton Dimensions (Length x Width x Height)	16 x 6 x 10 inches
Master Carton Weight	4.24 kg
SCC Codes	1073130432893 0
Units per Pallet	360.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95% non-condensing %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95% non-condensing %
Storage Elevation	0-15000 meters

Conformance

Approvals	FCC Part 15 Class B , MET Canada , MET USA
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$50000

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs