

Basic

Aspect Ratio:	16:9
Backlight Technology:	LED
Brand Name:	Acer
Brightness:	250 cd/m ²
Colour Support:	16.7 Million Colours
Contrast Ratio:	100,000,000:1
DVI:	Yes
HDMI:	Yes
Maximum Resolution:	1920 x 1080
Number of Screens:	1
Product Family:	S
Product Type:	LCD Monitor
Response Time:	4 ms GTG
Screen Mode:	Full HD
Screen Size:	60.5 cm (23.8")
VGA:	Yes

General Information

Brand Name:	Acer
Manufacturer Part Number:	UM.QS0EE.001
Manufacturer Website Address:	http://www.acer.co.uk
Manufacturer:	Acer, Inc
Product Model:	SA240Y
Product Name:	SA240Y Widescreen LCD Monitor
Product Series:	S
Product Type:	LCD Monitor

Interfaces/Ports

DVI:	Yes
HDMI:	Yes
VGA:	Yes

Miscellaneous

Package Contents:	<ul style="list-style-type: none">• SA240Y Widescreen LCD Monitor• Power Cord• 1 x VGA Cable
-------------------	--

Physical Characteristics

Depth with Stand:	212 mm
Depth:	36 mm
Height with Stand:	405 mm
Height:	323 mm
Weight (Approximate):	2.50 kg
Weight with Stand (Approximate):	2.86 kg
Width with Stand:	540 mm
Width:	540 mm

Power Description

Energy Consumption per Year:	28 kWh
Energy Efficiency Class:	A
Off-Mode Power Consumption:	400 mW
Operating Power Consumption (Energy Star):	24 W
Standby Power Consumption:	450 mW

Technical Information

Aspect Ratio:	16:9
Backlight Technology:	LED
Maximum Adjustable Height:	No
Number of Screens:	1
Panel Technology:	In-plane Switching (IPS) Technology
Response Time:	4 ms GTG
Screen Mode:	Full HD
Screen Size:	60.5 cm (23.8")
Swivel Angle:	No
Tilt Angle:	-5°to15°

Video

Brightness:	250 cd/m ²
Colour Support:	16.7 Million Colours
Contrast Ratio:	100,000,000:1
Maximum Resolution:	1920 x 1080

Standard Refresh Rate: 60 Hz

Warranty

Limited Warranty: 2 Year