


Coaxial Cable Connector 16_MCX-75-2-5/133_N

Description

Right angle cable plug

Interface standards
SUHNER-MCX75



Technical Data

Electrical Data

Impedance	75 Ω		
Interface frequency max.	6 GHz		
Frequency range	DC to 1 GHz	1 to 2.5 GHz	2.5 to 6 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0012 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU, RoHS	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00007524
Catalogue drawing	DOU-00007526
Assembly instruction	DOC-0000179474

Ordering Information

Bulk 100 pcs package	16_MCX-75-2-5/133_NH
Single package	16_MCX-75-2-5/133_NE

Additional Information

Suitable cables	ENVIROFLEX_179, RG_179_B/U, RG_187_A/U
-----------------	--