


Coaxial PCB Connector 85_BNC-50-0-1/133_N

Description

Right angle PCB jack

Interface Standards

IEC 60169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 4 GHz

Mechanical Data

Board mounting type through holes
Weight 0.0187 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00070952
Catalogue drawing DCA-00012658
Mounting hole DOU-00012084

Ordering Information

Single package 85_BNC-50-0-1/133_NE

Remarks

PCB connector with stand-offs