


KEMET, EFG2, Flex Suppressors, Commercial Grade



| General Information | |
|------------------------|--|
| Series: | EFG2 |
| Style: | Sheet |
| Description: | Flex Suppressor GHz Band High Performance Type |
| Features: | GHz Band High Performance Type, Wi-Fi, GPS, LTE-A |
| RoHS: | Yes |
| Qualifications: | UL94 HB, UL File No. E176124 |
| Environment: | RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free |

| Dimensions | |
|-------------------|-----------|
| Sheet Size | 240x240mm |
| L | 240mm NOM |
| W | 240mm NOM |
| T | 0.3mm NOM |

| Specifications | |
|-----------------------------|-------------|
| Temperature Range: | -40/+105C |
| Effective Frequency: | 10 GHz MAX |
| Resistance: | 1 MOhms MIN |
| Specific Gravity: | 3.9 Atm TYP |

| Packaging Specifications | |
|--------------------------|--------------------------|
| Tape Description: | Without PET Tape (Txx00) |
| Tape Thickness: | 0.03mm |