

Model	PEL00563	Heat Output	
Rated Voltage	220-240VAC	Nominal heat output P_{nom}	2.0-2.5kW
Frequency	50/60Hz	Min heat output P_{min}	1.0kW
Rated Power	2500W	Max heat output P_{max}	2.5kW
Auxiliary electricity consumption			
At nominal heat output el_{max}			0.01kW
At minimum heat output el_{min}			0.01kW
In standby mode el_{sb}			N/A
With mechanical thermostat room temperature control plus day timer			YES/YES