








# OSRAM LED ValueFlex LED Strip Selector

## Driver type by length required

## Drivers

Type	Strip Options	Driver Type	Driver type by length required						Drivers				
			1M	2M	3M	4M	5M	6M	30	60	50	80	1-10
300 Lumens, 2.0W/M IP20, IP66 6M	VF300-G3-827-06 / Farnell 2860762	On-Off Driver	[Yellow]						ELEMENT 30/220-240/24 - FARNELL 2860780	ELEMENT-60/220-240/24 - FARNELL 2860781	OTIDALI50/220-240/24 1-4CH FARNELL 2860777 1 Driver / Strip, No Parallel connection	OTIDALI80/220-240/24 1-4CH FARNELL 2860778 1 Driver / Strip, No Parallel connection	OT 80/220-240/24 DIMP FARNELL 2860779
	VF300-G3-840-06 / Farnell 2860763	DALI Driver	[Grey]										
	VFP300-G3-827-06 / Farnell 2860764	1-10V Driver	[Green]										
	VFP300-G3-840-06 / Farnell 2860765		[Green]										
800 Lumens, 6.42W/M IP20, IP66 6M	VF800S-G3-827-06 / Farnell 2860766	On-Off Driver	[Yellow]			[Blue]			ELEMENT 30/220-240/24 - FARNELL 2860780	ELEMENT-60/220-240/24 - FARNELL 2860781	OTIDALI50/220-240/24 1-4CH FARNELL 2860777 1 Driver / Strip, No Parallel connection	OTIDALI80/220-240/24 1-4CH FARNELL 2860778 1 Driver / Strip, No Parallel connection	OT 80/220-240/24 DIMP FARNELL 2860779
	VF800S-G3-840-06 / Farnell 2860767	DALI Driver	[Grey]										
	VFP800S-G3-827-06 / Farnell 2860768	1-10V Driver	[Green]										
	VFP800S-G3-840-06 / Farnell 2860769		[Green]										
1500 Lumens, 11.5W/M IP20, IP66 5M	VF1500-G3-827-05 / Farnell 2860770	On-Off Driver	[Yellow]		[Blue]			n/a	ELEMENT 30/220-240/24 - FARNELL 2860780	ELEMENT-60/220-240/24 - FARNELL 2860781	OTIDALI50/220-240/24 1-4CH FARNELL 2860777 1 Driver / Strip, No Parallel connection	OTIDALI80/220-240/24 1-4CH FARNELL 2860778 1 Driver / Strip, No Parallel connection	OT 80/220-240/24 DIMP FARNELL 2860779
	VF1500-G3-840-05 / Farnell 2860771	DALI Driver	[Grey]		[Orange]								
	VFP1500-G3-827-05 / Farnell 2860772	1-10V Driver	[Green]		[Green]								
	VFP1500-G3-840-05 / Farnell 2860773		[Green]		[Green]								

Power Feeders and Strip to Strip Connectors	Product Name	Image
	Feeder IP20 Strip To Driver Connector Farnell 2860774	
	Feeder IP54 Strip To Driver Connector Farnell 2860775	
	Jumper IP54 & IP20 In-Line Strip to Strip Connector Farnell 2860776	

Profiles to suit ALL the above	Product Name	Image
	Profile: FX-QMS-G1-TU16H12-300 4052899448964	
	Profile Diffuser Frosted: FX-QMS-G1-CFDL-300 4052899447059	
	Profile End Cap: FX-QMS-G1-EFGP-TU16H12LS 4052899449183	
	Profile Mounting Bracket: FX-QMS-G1-BMZI-DIV1 4052899446861	

Colour Definitions to aide selection	Colour	Description
	827 = Very Warm White	<b>Yellower:</b> For warm home lighting in kitchens, living rooms etc - Matches colour of filament lamps
	840 = Cool White	<b>Whiter:</b> For whiter light such as bathrooms, hair salons and offices - Matches typical office fluorescent colour