



Premier Series UHF Wireless Microphone System with (2) Handheld Mics, Dual Rechargeable Dock, 16-Channel Selectable Frequency, LCD Display, Rack Mountable

PDWM2560



## **Features:**

- UHF Band Receiver System
- Dual Microphone Charging Docks
- 16 Channel Selectable Frequency Design
- PLL-Synthesized Control Technique
- Broad Frequency Response Range & Low Distortion
- Up to 175' Feet Wireless Communication Range
- Integrated Noise Filtration System
- High Signal/Noise Ratio Performance
- AF Signal LED Indicators
- Independent Channel Adjustable Volume Controls
- LCD Digital Display with Channel & Frequency Readout
- Easy-to-Use Touch Button Controls
- Detachable Dual Antennas
- Rack Mountable System
- 1/4" XLR Unbalanced Audio Output Jack Connector
- (2) Mixed Balanced Output Jack Connectors

## **What's in the Box:**

- Receiver Base
- (2) Rechargeable Wireless Microphones
- Wall Power Adapter

## **Microphone:**

- LCD Display
- Built-in (2) 'AA' Rechargeable Batteries: 1000mAh
- Nominal Current Drain: <100mA
- Modulation Type: FM
- RF Output: >10dB,
- Max. Deviation: +/- 70 kHz
- Spurious Emission: >55dB
- Power On/Off Switch

## **System Receiver:**

- Audio Frequency Response: 100-18kHz
- T.H.D.: <1%
- Mobile State Range: 100dB
- Receiving Sensitivity: -105dBm
- Signal/Noise Ratio: >85dB
- Image & Spurious Rejection: >70dB
- Audio Output Level: +/- 300mV
- Frequency Stability: +/- 0.005%
- Maximum Deviation: +/- 15 kHz
- Receiver Dimensions: 8.5" x 6.7" x 2.0" inches
- Power Supply: DC 13-15V
- Sold as: Unit
- Weight: 6.48 lbs.