



Premier Series Professional UHF Microphone Rack Mountable System with (2) Plug-in XLR Wireless Transmitters and Selectable Frequencies

PDWM3450



System Features:

- LED Power Indicator & Channel Display
- Operation Range: Up to 164 ft.
- Audio Level Indicator for wireless system audio signal level
- Independent & adjustable channel volume controls
- RF Signal Indicator for transmitter signal strength
- Up to sixteen separate channels to choose from
- Includes two plug-in XLR wireless transmitters
- 1/4" Mixed audio output jack
- (2) Individual XLR balanced output jacks
- Individual Squelch controls
- AC/DC adapter power jack

- Power Supply: 110/220V
- Rack mountable system

Receiver Specs:

- Individual Balanced XLR Output
- Mixed ¼ Inch Output
- 16 operational wireless channels
- Individual Squelch controls for each channel
- RF Image Spurious Rejection >80 dB
- Receiving Sensitivity: -105 dB
- Signal/Noise Ratio: -90 dB
- Border Upon Chanel Rejection: >80 dB
- Power Requirements: 13-15V
- DC nominal 800 mA
- Dimensions: 19 in X 8.4 in X 1.7 in
- Fits in to standard 1 RU space

Plug-In Transmitter Specs:

- Includes (2) Plug-in Transmitters
- High/Low Gain Switch
- 16 operational wireless channels
- RF Output: >10 dBm
- Modulation Type: FM
- Max Deviation: \pm 68 kHz
- Spurious Emission: >55 dBc
- Nominal Current Drain: <100 mA
- +5.85 V Phantom power supply
- Power Requirements: 1 x 1.5 V AA
- Dimensions: 4.4 in X 1.15 in X 1.1 in
- Sold as: Kit
- Weight: 6.51 lbs.