



Professional Dynamic Microphone, Unidirectional Handheld Mic,
Includes XLR Audio Cable

PDMIC58



Features:

- Built-in Acoustic Pop Filter
- Ultra-Wide Frequency Response
- High Signal Output for Vocals & Singing
- Rugged Construction & Steel Mesh Grill
- Integrated Low Noise Circuitry
- Includes: 15' ft. XLR to 1/4" Audio Connection Cable
- Perfect for Stage Performances or In-Studio Use

Technical Specs:

- Mic Element/Type: Dynamic
- Pickup/Polar Pattern: Uni-Directional
- Mic Body Material: Zinc Alloy Metal
- Frequency Response: 50Hz-15KHz
- 600 Ohm Output Impedance (+/-)30%
- Microphone Sensitivity: -54dB (+/-)3db(0dB=1V/Pa @ 1KHz)
- Dimensions: Φ 1.96" x 6.41"
- Sold as: Unit
- Weight: 1.48 lbs.