

Power module - EMD-SL-PS- 24DC - 2885359

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Power modules, pluggable, for EMD-SL-..., supply voltage: 20 V DC ... 30 V DC

Why buy this product

- Separately adjustable startup and response delays
- Variable supply voltage range
- Adjustable via potentiometer on the front



Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 049887
GTIN	4046356049887
Weight per Piece (excluding packing)	21.000 g
Custom tariff number	85043180
Country of origin	Austria

Technical data

Dimensions

Width	32 mm
Height	35 mm
Depth	16 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C

Input data

Nominal input voltage	24 V DC
-----------------------	---------

Environmental Product Compliance

Power module - EMD-SL-PS- 24DC - 2885359

Technical data

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 5.0	27049002
eCl@ss 5.1	27049002
eCl@ss 6.0	27049002
eCl@ss 7.0	27049002
eCl@ss 8.0	27049002
eCl@ss 9.0	27040701

ETIM

ETIM 4.0	EC002540
ETIM 5.0	EC002540
ETIM 6.0	EC002540

UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121535
UNSPSC 11	39121535
UNSPSC 12.01	39121535
UNSPSC 13.2	39121004

Approvals

Approvals

Approvals

EAC / EAC

Ex Approvals

Approval details

EAC		RU C- DE.A*30.B.01082
-----	---	--------------------------

Power module - EMD-SL-PS- 24DC - 2885359

Approvals

EAC



EAC-Zulassung