





P2662B Series



Specifications

Plunger	Hardened BeCu
Body	Gold-plated phosphorous bronze
Spring	Silver-plated BeCu
Ball	Stainless steel
Electrical Resistance	<30mΩ
Maximum Current	3 amps
Working Travel050" (1.27)


Spring Force in oz. (grams)	Initial	Working
Standard:	1.0 (28)	1.8 (51)
Alternate:	0.5 (14)	2.5 (71)



Pogo® Receptacle

The P2662B Series is designed to be used with the PR261 Series receptacles below. The recommended mounting hole is .035/.0365 (0.89/0.93mm). The recommended drill is a #64 or 0.92mm. Use tool T261-0 for installation.

PR261-0 Crimp




PR261-0F (Flush Mount)





PR261-1 Solder

PR261-1F (Flush Mount)



Receptacle with Probe



Dimensions in inches (millimeters).