

EAO – Your Expert Partner for Human Machine Interfaces

K14-131.121031 - Illuminated pushbutton

K14-131.121031 - Illuminated pushbutton



Attention: The preview is based on a sample product. This can differ from your current configuration.

Mounting

Mounting cut-out Ø 22,3 mm
Design raised

Front

Front dimension Ø 29 mm
Front shape round

Other Attributes

Weight 0.021 kg
Operation current 4/7 mA ±15 %
Operating voltage 24 V AC/DC

Operating-/Indication part

Lens illumination illuminative
Lens material Plastic
Lens optics transparent
Lens profile raised
Lens colour green

IP-Rating

Front protection IP67

Connection Method

Terminal Soldering terminal

Actuator

Switching action Momentary
Housing colour black
Housing material Plastic

Switching element

Switching system Snap-action switching element
Switching current 5 A
Contacts 1 NC + 1 NO
Switching voltage 250 V AC/DC
Contact material

Illumination

LED colour green


Function

Illuminated pushbutton


EAO – Your Expert Partner for Human Machine Interfaces

K14-131.121031 - Illuminated pushbutton


Dimensions



Mounting cut-outs



Wiring diagram



Legend

Contacts: NC = Normally closed, NO = Normally open