


6-Lobe Pin



6-Lobe Pin - Button Head Self Tapping Screws - A2 Stainless Steel



Dimensions (mm)

SCREW TYPE 6-LOBE PIN	AB TYPE SELF TAPPING SCREWS						
	No. 4	No. 6	No. 8	No. 10	No. 12	No. 14	
DIMENSIONS	2.9mm	3.5mm	4.2mm	4.8mm	5.5mm	6.3mm	
BUTTON HEAD		5.5	6.7	7.4	9.3	10.2	11.0
		1.5	2.6	2.2	2.6	3.1	3.4

Material and Finish

Material: A2 (304) Stainless Steel
Heat Treatment: None
Finish: Passivated

Part Numbers & Driver Size

GAUGE	LENGTH	3/8"	1/2"	5/8"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"	DRIVER SIZE
		9.5mm	13mm	16mm	19mm	25mm	32mm	38mm	50mm	63mm	75mm	
4	2.9mm		RTBS04D		RTBS04F							T10
6	3.5mm	RTBS06C	RTBS06D	RTBS06E	RTBS06F	RTBS06G		RTBS06I	RTBS06J			T10
8	4.2mm	RTBS08C	RTBS08D	RTBS08E	RTBS08F	RTBS08G	RTBS08H	RTBS08I	RTBS08J			T15
10	4.8mm	RTBS10C	RTBS10D	RTBS10E	RTBS10F	RTBS10G	RTBS10H	RTBS10I	RTBS10J			T25
12	5.5mm					RTBS12G	RTBS12H	RTBS12I	RTBS12J	RTBS12K	RTBS12L	T27
14	6.3mm				RTBS14F	RTBS14G	RTBS14H	RTBS14I	RTBS14J			T30

Additional Information

Installation: 6-Lobe Pin - see video
Removal: 2-Way Removable Screw

Hafren
6-Lobe Pin

- ✓ 6-Lobe drive with internal pin
- ✓ High torque drive
- ✓ Available in multiple heads & threads
- ✓ Stocked in the largest range available

Every effort has been made to ensure the accuracy of information provided in this datasheet. Hafren Fasteners cannot warrant the information however, expressly or implied, and any liability arising from it is expressly excluded. Customers must satisfy themselves as to the suitability of products and the technical information relating to them, and it is recommended that you conduct your own tests to establish suitability. All sizes shown are in mm without min and max tolerances and are guide sizes. Hafren Fasteners reserve the right to change/alter sizes without notice. This does not effect your statutory rights.

6-Lobe Pin



Weight per Pack


GAUGE	LENGTH	3/8"	1/2"	5/8"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"	DRIVER SIZE
		9.5mm	13mm	16mm	19mm	25mm	32mm	38mm	50mm	63mm	75mm	
4	2.9mm		Box 9 65g		Box 9 84g							T10
6	3.5mm	Box 9 85g	Box 9 107g	Box 9 128g	Box 9 142g	Box 9 168g		Box 18 240g	Box 18 298g			T10
8	4.2mm	Box 9 113g	Box 9 133g	Box 9 159g	Box 9 173g	Box 12 214g	Box 12 268g	Box 18 305g	Box 18 407g			T15
10	4.8mm	Box 9 164g	Box 9 206g	Box 9 224g	Box 12 251g	Box 12 314g	Box 18 377g	Box 18 428g	Box 22 532g			T25
12	5.5mm					Box 18 420g	Box 18 518g	Box 18 580g	Box 22 752g	Box 27 920g	Box 27 1,085g	T27
14	6.3mm				Box 18 452g	Box 18 545g	Box 18 675g	Box 22 769g	Box 22 989g			T30

*All parts packed in 100pcs - Please see below Pack Dimension guide

Box Dimensions Guide

DIMENSION	BOX 9	BOX 12	BOX 18	BOX 22	BOX 27	BOX 30	BOX 32
	A	51mm	57mm	71mm	81mm	89mm	101mm
B	32mm	36mm	47mm	54mm	68mm	76mm	82mm
C	55mm	66mm	90mm	111mm	124mm	128mm	171mm

Cardboard Box



Every effort has been made to ensure the accuracy of information provided in this datasheet. Hafren Fasteners cannot warrant the information however, expressly or implied, and any liability arising from it is expressly excluded. Customers must satisfy themselves as to the suitability of products and the technical information relating to them, and it is recommended that you conduct your own tests to establish suitability. All sizes shown are in mm without min and max tolerances and are guide sizes. Hafren Fasteners reserve the right to change/alter sizes without notice. This does not effect your statutory rights.