


## 6-Lobe Pin - Pan Head Self Drilling Screws



### Self Drilling Screws Technical Info (mm)

HEAD STYLE		GAUGE	No. 8	No. 10	No. 12
			4.2mm	4.8mm	5.5mm
PAN HEAD			7.9	9.3	10.6
			2.9	3.4	3.9
POINT SIZE			2	3	3
MATERIAL THICKNESS Mild Steel up to (mm)			1 + 2	2 + 2	2 + 3

All sizes shown are without min and max tolerances and are guide sizes.

### Material and Finish

**Material:** Steel C1022  
**Heat Treatment:** Hardened  
**Finish:** Delta Protekt

### Part Numbers, Size & Tooling

GAUGE	LENGTH	1/2"	3/4"	1"	1 1/2"	2"	DRIVER SIZE
		13mm	19mm	25mm	38mm	50mm	
8	4.2mm	RTPD08D -DP	RTPD08F -DP	RTPD08G -DP	RTPD08I -DP		T20
10	4.8mm		RTPD10F -DP	RTPD10G -DP	RTPD10I -DP	RTPD10J -DP	T25
12	5.5mm			RTPD12G -DP	RTPD12I -DP	RTPD12J -DP	T27

\*All parts Packed in 100pcs - Please see below Pack Dimension guide for sizes


### Additional Information

**Patented Product:** Hafren Fasteners

**Installation:** 6-Lobe Pin - see video

**Removal:** 2-Way Removable Screw

- ✓ No need to pre-drill
- ✓ Fast installation
- ✓ 6-Lobe Pin security drive
- ✓ Delta Protekt Coated Steel
- ✓ Pan and Countersunk Head



Every effort has been made to ensure the accuracy of information provided in this datasheet. Hafren Fasteners cannot warrant the information however, expressly or implied, and any liability arising from it is expressly excluded. Customers must satisfy themselves as to the suitability of products and the technical information relating to them, and it is recommended that you conduct your own tests to establish suitability. All sizes shown are in mm without min and max tolerances and are guide sizes. Hafren Fasteners reserve the right to change/alter sizes without notice. This does not effect your statutory rights.


## Pack Weight (100pcs) & Box Type

GAUGE	LENGTH	1/2"	3/4"	1"	1 1/2"	2"	DRIVER SIZE
		13mm	19mm	25mm	38mm	50mm	
8	4.2mm	Box 9 150g	Box 9 195g	Box 12 235g	Box 18 330g		T20
10	4.8mm		Box 12 270g	Box 12 320g	Box 18 445g	Box 18 550g	T25
12	5.5mm			Box 18 450g	Box 18 600g	Box 22 745g	T27

\*All parts Packed in 100pcs - Please see below Pack Dimension guide for sizes

## Pack Dimensions Guide

DIMENSION	BOX SIZE	BOX 9	BOX 12	BOX 18	BOX 22	BOX 27	BOX 30	BOX 32
	A		51mm	57mm	71mm	81mm	89mm	101mm
B		32mm	36mm	47mm	54mm	68mm	76mm	82mm
C		55mm	66mm	90mm	111mm	124mm	128mm	171mm



Every effort has been made to ensure the accuracy of information provided in this datasheet. Hafren Fasteners cannot warrant the information however, expressly or implied, and any liability arising from it is expressly excluded. Customers must satisfy themselves as to the suitability of products and the technical information relating to them, and it is recommended that you conduct your own tests to establish suitability. All sizes shown are in mm without min and max tolerances and are guide sizes. Hafren Fasteners reserve the right to change/alter sizes without notice. This does not effect your statutory rights.