

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2451361020](#)  
**Status:** **Active**  
**Overview:** [Mega-Fit Power Connectors](#)  
**Description:** Mega-Fit-to-Mega-Fit Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, 2.0m Length, Gold (Au) Plated, 10 Circuits, Black

**Documents:**

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                             |   |
|-----------------------------|---|
| Product Family              | Cable Assemblies                          |
| Series                      | <a href="#">245136</a>                    |
| Application                 | Power, Wire-to-Board                      |
| Assembly Configuration      | Dual Ended Connectors                     |
| Connector to Connector      | Mega-Fit-to-Mega-Fit                      |
| Overmolded                  | Yes                                       |
| Overview                    | <a href="#">Mega-Fit Power Connectors</a> |
| Product Literature Order No | 987651-4662                               |
| Product Name                | Mega-Fit OTS                              |
| UPC                         | 191128799089                              |

**Physical**

|                                |                      |
|--------------------------------|----------------------|
| Cable Length                   | 2.0m                 |
| Circuits (Loaded)              | 10                   |
| Color - Resin                  | Black                |
| Gender                         | Female-Female        |
| Lock to Mating Part            | Yes                  |
| Material - Metal               | Copper Alloy         |
| Material - Plating Mating      | Gold                 |
| Material - Plating Termination | Matte Tin            |
| Material - Resin               | PBT                  |
| Packaging Type                 | Bag                  |
| Pitch - Mating Interface       | 5.70mm               |
| Plating min - Mating           | 0.381µm              |
| Plating min - Termination      | 0.381µm              |
| Single Ended                   | No                   |
| Termination Interface: Style   | Crimp or Compression |
| Wire Insulation Diameter       | 15.50mm              |
| Wire Size AWG                  | 12                   |
| Wire/Cable Type                | UL 2464              |


**Electrical**

|                               |         |
|-------------------------------|---------|
| Current - Maximum per Contact | 16.0A   |
| Voltage - Maximum             | 300V AC |

**Material Info**

**Reference - Drawing Numbers**

|               |                |
|---------------|----------------|
| Sales Drawing | 2014400081-000 |
|---------------|----------------|



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[245136](#) Series

**Mates With**

Mega-Fit Header [76825](#) , [76829](#) , [172064](#) , [172065](#)