



43" Platinum Android Smart Freeview T2 HD LED TV

- 43" Platinum Full HD widescreen LED TV
- Android Smart TV with built-in Wi-Fi (Download all of your favourite Android apps to the TV)
- USB 2.0 – record digital TV and play media files from other devices
- 6 x Speakers (4 x 4ohm 8W sub-woofers, 2 x 8ohm 8W treble) max output 16W
- Air mouse remote control
- HDMI x 2 inputs for external devices & consoles
- Can be wall mounted (200mm x 200mm bracket not included)

	EAN	5060062267341
General Feature	Model No.	P43ANSMT
	Panel (60Hz/120Hz)	HV430FHB-N40
	Destination Country	UK
	Screen Size	43 inch LED Panel (Approx. 109cm)
	Max. Resolution	1920 x 1080 Full HD
	Contrast Ratio (Typical)	4000:1
	Brightness(TYP cd/m2)	230
	Display Colors	16.7M
	Viewing Angle(L/R/U/D)	CR≥10)89/89/89/89
	Cabinet Color	Silver
	Wall Mounting Support(Screw Size)	200 x 200mm (M5 x 10)
Reception	TV System	ATV: PAL BG/DK/I SECAM BG/DK/L/L' DTV:DVB-T & DVB-C&DVBT2, MPEG 2,MP@ML, MPEG 4
	5V from Antenna	N/A
	Number of channel for storing	100 Analog / 400 Digital
Sound	Bass	Yes
	Treble	Yes
	Balance	Yes
	Sound Mode	Standard / Music /Movie / Sports /User
	Stereo System	NICAM/A2
	Audio Output	4 x 8W for Bass/2 x 8W for Treble
	Speaker Distortion	<=5% Max
	Number of Speaker	4 x 4ohm for Bass/2 x 8ohm for Treble

Connectors Jack	RF Antenna	Yes x 1
	HDMI	Yes x 2
	CVBS	Yes x 1
	PC In	Yes x 1
	Audio In	PC audio x 1 (3.5 φ Mini Jack) Audio x1 (Shared with Ypbpr)
	Scart	N/A
	YPbPr	YES x 1 (3.5 φ Mini Jack)
	Digital Audio out	Yes Optical
	Earphone Out	Yes x 1
	USB on TV	Yes x 1
	CI	Yes x 1
	RCA	N/A
	RJ45 on Android	Yes x 1
	Mirco SD card on Android	Yes x 1
USB on Android	Yes x 2	
Andriod	SOC	M9280 PBM, ARM Cortex A7 quad core
	RAM	1GB DDR3
	CPU	6 core ARM Mali-450MP4
	Built-in Flash	4GB
	Wi-Fi	802.11 b/g/n
	OS	Android 4.4.4
Other Features	APS	ATV, DVBT, DVBC storage in capture order
	OSD Language	English, Deutsch, Norge, Dansk, Svenska, Francais, Espanol, Portugese, Italian
	EPG (Electronic Program Guide)	7 days
	Automatic Tuning	Yes
	Sleep Timer	YES (240min)
	Color Temperature Adjustment	Yes
	Picture Mode	Standard / Dynamic / Mild / User
	Home Mode	Yes
	Wifi on Android	Yes
Hotel Mode	Yes	
Power	Power Supply	AC 100V-240V~ 50Hz/60Hz
	Operation Power Consumption	55W
	KWh/annum	80kWh
	Max power Consumption	80W
	Standby Power Consumption	<0.5W
	Energy Efficiency Class	A
Accessories	Quick Start Guide	Yes
	Remote Control	Yes
	Power Cable	Yes
	Warranty	Yes
	Battery	1.5V (AAA)×2
Dimension	Unit Dimension With Stand (W x H x D mm)	969 x 681 x 257
	Unit Dimension Without Stand (W x H x D mm)	969 x 631 x 86
	Weight of unit (kg)	9.44
	Gift Box Dimension (W x H x D mm)	1065 x 726 x 151
	Weight of gift box with content (kg)	12.58
	Weight of carton/paper (kg)	2
	Weight of styrofoam (kg)	1