



**50" Platinum 4K UHD
Android Smart Freeview
T2 HD LED TV**

- 50" Platinum 4K Ultra HD widescreen LED TV
- Android Smart TV with built-in Wi-Fi (Download all of your favourite Android apps to the TV)
- USB 2.0 – play media files from other devices
- 6 x Speakers (4 x 4ohm 8W sub-woofers, 2 x 8ohm 8W treble) max output 16W
- Air mouse remote control
- HDMI x 3 inputs for external devices & consoles
- Can be wall mounted (400mm x 400mm bracket not included)

	EAN	5060062267358
General Feature	Model No.	P50ANSMT-4K
	Panel (60Hz/120Hz)	V500DJ2
	Destination Country	UK
	Screen Size	50 inch LED Panel (Approx. 127cm)
	Max. Resolution	3840 x 2160 UHD 4K
	Contrast Ratio (Typical)	4000:1
	Brightness(TYP cd/m2)	200
	Display Colors	1.07G
	Viewing Angle(L/R/U/D)	CR≥10)89/89/89/89
	Cabinet Color	Silver
	Wall Mounting Support(Screw Size)	400 x 400mm / M6 x 10

Reception	TV System	"DTV:DVB-T & DVB-C&DVBT2, MPEG 2,MP@ML,
	MPEG 4"	MPEG 4"
	5V from Antenna	N/A
	Number of channel for storing	400 Digital

Sound	Bass	Yes
	Treble	Yes
	Balance	Yes
	Sound Mode	Standard / Music /Movie / Sports /User
	Stereo System	NICAM/A2
	Audio Output	4 x 8W for Bass/2 x 8W for Treble
	Speaker Distortion	<=5% Max
	Number of Speaker	4 x 4ohm for Bass/2 x 8ohm for Treble

Connectors Jack	RF Antenna	Yes
	HDMI	Yes x 3
	CVBS	Yes x 1
	PC In	N/A
	Audio In	Yes x 1
	Scart	N/A
	YPbPr	N/A
	Digital Audio out	Yes Optical
	Earphone Out	N/A
	USB on TV	Yes x 1
	CI	N/A
	RCA	Yes x 1
	RJ45 on Android	Yes x 1
	Mirco SD card on Android	Yes x 1
USB on Android	Yes x 1	

Andriod	SOC	M9280 PBM, ARM Cortex A7 quad core
	RAM	1GB DDR3
	CPU	6 core ARM Mali-450MP4
	Built-in Flash	4GB
	Wi-Fi	802.11 b/g/n
	OS	Android 4.4.4

Other Features	APS	DVBT, DVBC storage in capture order
	OSD Language	English, Deutsch, Norge, Dansk, Svenska, Francais, Espanol, Portugese, Italian
	EPG (Electronic Program Guide)	7 days
	Automatic Tuning	Yes
	Sleep Timer	YES (240min)
	Color Temperature Adjustment	Yes
	Picture Mode	Standard / Dynamic / Mild / User
	Home Mode	Yes
	Wifi on Android	Yes
	Hotel Mode	Yes

Power	Power Supply	AC 100V-240V~ 50Hz/60Hz
	Operation Power Consumption	85W
	KWh/annum	120kWh
	Max power Consumption	120W
	Standby Power Consumption	<0.5W
	Energy Efficiency Class	A

Accessories	Quick Start Guide	Yes
	Remote Control	Yes
	Power Cable	Yes
	Warranty	Yes
	Battery	Yes

Dimension	Unit Dimension With Stand (W x H x D mm)	1106 x 765 x 286
	Unit Dimension Without Stand (W x H x D mm)	1106 x 710 x 90
	Weight of unit (kg)	12.75
	Gift Box Dimension (W x H x D mm)	1230x 840 x 160
	Weight of gift box with content (kg)	16.55
	Weight of carton/paper (kg)	3
	Weight of styrofoam (kg)	0.45