



K2

Model Name: K242HQLC
Part Number: UM.UX6EE.C01

Eco-friendly Acer K2 Series monitors are affordable display solutions for everyday PC usage. They offer hassle-free usability without compromising image quality. The intelligent design brings together a multitude of connection ports, superb performance, and eco-friendliness – all at a price point that'll make you smile.



Screen Size

23.6"

Resolution

Full HD (1920 x 1080)

Aspect Ratio

16:9

Response Time

4 ms GTG

Refresh Rate

60 Hz

Colour Support

16.7 million

Contrast Ratio

100,000,000:1

Brightness

300 cd/m²

Backlight

LED

Panel Type

Twisted Nematic Film (TN Film)

Stand

Tiltable (-5° to 25°)

Ports & Connectors

DVI-in

HDMI®-in

VGA

Power

22 W (ENERGY STAR® rating)

27 W (EEL)

450 mW (standby)

350 mW (off)

Environmental Certification

MPR II

Colours

Black

Dimensions (H x W x D)

13.22" x 22.32" x 2.39" (without stand)

16.6" x 22.3" x 8.6" (with stand)

Weight (Approximate)

8.6 lbs. (without stand)

9.3 lbs. (with stand)

Package Contents
K242HQL Widescreen LCD Monitor
Power Cord
1 x VGA Cable

?_Warranty

[Standard Warranty.](#)