

## TC10PM

For Indoor Use

TC10PM is ideal for spot cooling in a small to medium-sized space. The 10L unit has an easy-access water fill door that helps for pain-free refilling.

The TC10PM has four durable caster wheels, and is lightweight which allows you to easily roll the unit from room to room. Depending on your needs the unit has three functional speeds.



Product Dimensions (in): 11.6 (W) 11.0 (D) 29.6 (H)  
Net Weight: 4.9 kg / 10.8 lbs



Easy-to-Use Controls

## FEATURES & BENEFITS



Low Power Consumption  
40 Watts\*



Water Capacity  
10 L\*\*



Cools Up To  
120 Sq.ft (11 Sq. m)\*



Powerful Air Flow  
194 CFM (330 m<sup>3</sup>/hr)\*



3 Speeds:  
Low / Medium / High



Slim Design



Wheels for Easy Mobility



Water Fill Door



Honeycomb  
Cooling Media and  
Mesh Filter



Oscillating Louvers

Find out more about evaporative air coolers:  
[www.honeywellhomecomfort.com](http://www.honeywellhomecomfort.com)

\* All specifications mentioned are under test conditions, actual performance depends on ambient conditions. Specifications may vary in different countries and subject to change without prior notice.  
\*\* Water Capacity is the total volume of water that can be contained within the air cooler water tank and water distribution system.

### Scott Brothers Ltd

1 Whiteside Station Road  
Holmes Chapel Cheshire  
CW4 8AA  
UK  
Email: [enquiries@scottbrothersltd.co.uk](mailto:enquiries@scottbrothersltd.co.uk)  
Telephone: +44 (0) 1477 539 500

© 2018 JMATEK Limited.  
All rights reserved. The Honeywell  
Trademark is used under license  
from Honeywell International Inc.  
Honeywell International Inc. makes  
no representations or warranties  
with respect to this products  
This product is manufactured by  
JMATEK Limited.