


960H Indoor Dome Camera with Built-In IR LEDs

- CLED32D7B** 3.6mm fixed lens, black housing
- CLED32D7W** 3.6mm fixed lens, white housing
- CLED32D1B** 2.8-12mm auto iris varifocal lens, black housing
- CLED32D1W** 2.8-12mm auto iris varifocal lens, white housing

Features

- 700 TV lines of resolution
- IR Range: 65'
- 3-axis design, both wall and ceiling mountable
- 12VDC operation
- 5 year warranty



Specifications

- Image Sensor 1/3" color 960H CCD
- Resolution..... 700 TV lines
- Minimum Illumination..... 0 lux with IR on
- S/N Ratio 50dB
- Effective Pixels 976 (H) x 494 (V)
- Total Pixels 1020 (H) x 508 (V)
- Shutter 1/60 sec. – 1/120,000 sec.
- Number of IR LEDs 24
- IR Range 65 ft. (depending on scene reflection)
- Synchronization Internal
- DNR..... Low
- White Balance ATW
- TV System NTSC
- Housing High impact ABS
- Operating Temperature.. 14° F - 122° F
- Power Supply 12VDC (power supply not included)
- Power Consumption 250mA
- Dimensions..... 4.4" (Dia.) x 3.4" (H)
- Weight 8 oz.
- Included in Package Main unit, mounting screws, test monitor lead,
DC lead, user manual

Optional Accessory



PSW5
12VDC
Power Supply