


960H Dual Voltage Indoor Dome Camera with Built-In IR LEDs

- HLED33D7B** 3.6mm fixed lens, black housing
- HLED33D7W** 3.6mm fixed lens, white housing
- HLED33D1B** 2.8-12mm auto iris varifocal lens, black housing
- HLED33D1W** 2.8-12mm auto iris varifocal lens, white housing

Features

- 700 TV lines of resolution
- IR Range: 65'
- Smart DNR reduces noise in low light
- Smart IR reduces saturation of objects within close proximity to IR LEDs
- 3-axis design, both wall and ceiling mountable
- Digital wide dynamic range
- OSD for camera setting adjustments
- 12VDC/24VAC dual voltage operation
- 5 year warranty



Specifications

Image Sensor 1/3" color 960H CCD
 Resolution..... 700 TV lines
 Minimum Illumination..... 0 lux with IR on
 S/N Ratio 50dB
 Effective Pixels 976 (H) x 494 (V)
 Total Pixels 1020 (H) x 508 (V)
 Shutter 1/60 sec – 1/120,000 sec
 Number of IR LEDs 24
 IR Range 65 ft. (depending on scene reflection)
 OSD..... Yes
 Synchronization Internal
 Privacy..... On / Off (8 zones)
 Motion Detection..... On / Off (4 zones)
 Mirror On / Off

DNR..... High / Middle / Low / Off
 White Balance ATW / Push / Manual
 Image..... BLC / HLC / D-WDR / Defog
 AGC..... Level adjustable (0-20)
 TV System..... NTSC
 Housing High impact ABS
 Operating Temperature.. 14° F - 122° F
 Power Supply 12VDC, 24VAC (power supply not included)
 Power Consumption 250mA
 Dimensions..... 4.4" (Dia.) x 3.4" (H)
 Weight 8 oz.
 Included in Package Main unit, mounting screws, test monitor lead, DC lead, user manual

Optional Accessories



PSW4
24VAC
Power Supply



PSW5
12VDC
Power Supply