



3MP Bullet IP Camera with Junction Box

O3VLB3

2.8mm fixed lens, dark gray housing



Features

- Supports 3MP @ 20fps and 1080p @ 30fps
- Built-in standard PoE (IEEE 802.3af)
- Adaptive IR LEDs reduce IR saturation
- IR Range: 98' (depending on scene reflection)
- True Day/Night operation (IR cut filter)
- IP67 compliant, weather resistant
- UL listed
- Junction box included
- Conformant with ONVIF profile S
- 5 year warranty*



Included Junction Box (O2VLBB)



Camera Specifications

Image Sensor	Progressive scan 1/3" CMOS, 3MP
Maximum Resolution	2304 x 1296
Minimum Illumination	F2.0, Color: 0.37 lux, BW: 0 lux
Field of View (H)	98°
IR Range	98' (depending on scene reflection)
White Balance	Auto, Manual
Exposure Control	Yes
Digital Slow Shutter	Yes
Compensation	BLC / HLC / DWDR
Day/Night	IR cut filter
DNR	3D

Video Specifications

Main Resolution	2048x1296 / 1920x1080 / 1280x720 @ 30fps
Compression	H.264 (HP/MB/BP), MJPEG
Bitrate Control	VBR, CBR
Multiple Streaming	2 streams

Network Specifications

Protocols	IPv4/IPv6, TCP, UDP, RTP, RTSP, HTTP, HTTPS, SMTP, FTP, DHCP, DNS
DDNS Support	Speco DDNS (free of charge)
Security	User ID & Password protection, IP address filtering, digest authentication, user access log, HTTPS
User Access	20 simultaneous users (performance may vary depending on resolution)

Client Specifications

Web Browser Support	Windows (Internet Explorer 8 and up, Chrome, Firefox)
PC Application	SecureGuard® VMS
Mobile	SecureGuard® Mobile (iPhone® and Android™)

External Terminal Specifications

Ethernet	10/100 Mbps
Power	DC jack

System Specifications

PoE	Standard (IEEE 802.3af)
Analytics	Motion detection (4 regions), tamper detection
Alarm Triggers	Analytics
Alarm Events	Email, record, snapshot
Video Buffer	Configurable pre-record & post-record
Image Settings	Privacy mask, corridor mode

Operating & Unit Specifications

Power	PoE, 12VDC (power supply not included)
Power Consumption	4W max.
Operating Temperature	-20°F - 140°F
Operating Humidity	0% - 95% RH
Unit Dimensions	2.75" (Dia.) x 6.49" (L)
Unit Weight	13 oz.
Certifications	FCC, RoHS
Included in Package	Unit, CD (manual, software), mounting screws, L wrench

Optional Accessories



O3PMT Pole Mount (use with O2VLWM)



POEINJ 12.95W PoE Injector



PSW5 12VDC Power Supply

* Effective on all new purchases as of 2/1/17. Visit specotech.com for latest ONVIF® support. ONVIF is a trademark of Onvif, Inc. iPhone and iPad are trademarks of Apple Inc., registered in the U.S. and other countries. Android is a trademark of Google Inc. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 2/6/18

