

- Universal input voltage
- Compact and light weight
- Efficiency level VI
- Mains plug not included
- Exchangeable AC plugs
- Exchangeable DC plugs
- Universal inngangsspenning
- Kompakt enhet, lett vekt
- Effektivitetsnivå VI
- Nettplugg ikke inkludert
- Utskiftbare AC plugger
- Utskiftbare DC plugger

**Technical specifications****Tekniske data**

Input voltage:	Inngangsspenning:	90-264 VAC, 50/60 Hz
Line frequency:	Frekvensområde:	47-63 Hz
Max. output power:	Maks. utgangseffekt:	25 W
Load regulation:	Lastregulering:	4-5 %
Mains regulation:	Linjeregulering:	< 1 %
Ripple:	Rippel:	2% max
Efficiency, approx.:	Virkningsgrad, ca.:	> 86,35% (avg. of 25,50,75 and 100% load) 24V: > 87%
Standby power:	Tomgangseffekt:	≤ 0,1 W
Hold up time:	Hold up time:	12 ms (min)
Temperature range	Temperaturområde	
• Operating:	• Drift:	-20°C - +40°C
• With derating:	• Med derating:	+70°C
• Storage:	• Lagring:	-40°C - +85°C
Derating:	Derating:	0,42W/°C over 40°C
Insulation class:	Isolasjonsklasse:	II
Insulation voltage	Isolasjonsspenning	
• Primary - secondary:	• Primær - sekundær:	4242VDC (min)
Safety:	Sikkerhet:	EN 60950
EMC standards	EMC standarder	
• Emission:	• Emisjon:	EN 61000-6-3
• Immunity:	• Immunitet:	EN 61000-6-1
Reliability (MIL-HDBK-217F):	Pålitelighet (MIL-HDBK-217F):	MTBF > 100.000 hrs at 25°C
Output terminal:	Utgangsterminal:	1,2 m cable with exchangeable output plug 1,2 m sekundærledning med utskiftbar plugg
Dimensions (LxWxH):	Ytre mål (LxBxH):	75 x 43 x 40 mm
Weight:	Vekt:	125 g


Voltage versions - Spenningsversjoner

Output (V) Utgang (V)	Max. current (A) Maks. strøm (A)	Max. output power (W) Maks. utgangseffekt (W)
12	2,08	25
24	1,04	25

Safety approvals - Godkjenninger

AC/DC Switch Mode Power Supplies

Ordering Information



Note: The suffix “5000” denotes standard catalogue units which are re-packed to create the Farnell specification numbers.

Part Number Table

Description	Part Number
Power Supply, 25W Plug Top, 12V 2.08A	6322125000
Power Supply, 25W Plug Top, 24V 1.04A	6322245000

Important Notice : This data sheet and its contents (the “Information”) belong to the members of the Premier Farnell group of companies (the “Group”) or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group’s liability for death or personal injury resulting from its negligence. element14 is the registered trademark of the Group. © Premier Farnell Limited 2016.