

## LED Floodlights



VT-100-B

### HIGHLIGHTS :

WATTS



100

EQ. WATTS



100

LUMINOUS



8000

BEAM ANGLE



100

### PRODUCT FEATURES

Item No	:	VT-100-B
SKU Code	:	413
Watts	:	100
Voltage	:	AC:220-240V,50Hz
Lumen(lm)	:	8000
Color Temperature	:	4000K
Beam Angle	:	100
PF	:	>0.9
LED Chip Type	:	SMD-Samsung Chip
CRI	:	>80
Certification	:	EMC,LVD,ROHS
IP Rating Protection Class	:	IP65
Body type	:	Die casting Aluminium
Dimmable	:	-
Life Time	:	30,000 Hours
Operation Temperature	:	-25 to +45°C
EAN code	:	3800157629119
Unit size	:	291x240x30mm
Packing details	:	4.00
Unit cbm	:	0.00380