

LED Floodlights



VT-10-B

HIGHLIGHTS :

WATTS



10

EQ. WATTS



100

LUMINOUS



800

BEAM ANGLE



100

PRODUCT FEATURES

| | | |
|----------------------------|---|------------------|
| Item No | : | VT-10-B |
| SKU Code | : | 426 |
| Watts | : | 10 |
| Voltage | : | AC:220-240V,50Hz |
| Lumen(lm) | : | 800 |
| Color Temperature | : | 6400K |
| Beam Angle | : | 100 |
| PF | : | >0.9 |
| LED Chip Type | : | SMD-Samsung Chip |
| CRI | : | >80 |
| Certification | : | EMC,LVD,ROHS |
| IP Rating Protection Class | : | IP65 |
| Body type | : | DIECAST ALUMINUM |
| Dimmable | : | - |
| Life Time | : | 30,000 Hours |
| Operation Temperature | : | -25 to +50°C |
| EAN code | : | 3800157630825 |
| Unit size | : | 115x108x26mm |
| Packing details | : | 20.00 |