

## LED Floodlights



VT-200-B

### HIGHLIGHTS :

WATTS



200

EQ. WATTS



LUMINOUS



16000

BEAM ANGLE



100

### PRODUCT FEATURES

|                            |   |                       |
|----------------------------|---|-----------------------|
| Item No                    | : | VT-200-B              |
| SKU Code                   | : | 418                   |
| Watts                      | : | 200                   |
| Voltage                    | : | AC:220-240V,50Hz      |
| Lumen(lm)                  | : | 16000                 |
| Color Temperature          | : | 4000K                 |
| Beam Angle                 | : | 100                   |
| PF                         | : | >0.9                  |
| LED Chip Type              | : | SMD-Samsung Chip      |
| CRI                        | : | >80                   |
| Certification              | : | EMC,LVD,ROHS          |
| IP Rating Protection Class | : | IP65                  |
| Body type                  | : | Die casting Aluminium |
| Dimmable                   | : | -                     |
| Life Time                  | : | 30,000 Hours          |
| Operation Temperature      | : | -25 to +45°C          |
| EAN code                   | : | 3800157629157         |
| Unit size                  | : | 439x346x56mm          |
| Packing details            | : | 2.00                  |
| Unit cbm                   | : | 0.01420               |