

LED Panel Series



VT-615RD

HIGHLIGHTS :

WATTS



15

EQ. WATTS



120

LUMINOUS



1500

BEAM ANGLE



120

Item No	:	VT-615RD
SKU Code	:	621
Watts	:	15
Voltage	:	AC:220-240V,50Hz
Lumen(lm)	:	1500
Color Temperature	:	4000K
Beam Angle	:	120
Commercial type	:	Round
PF	:	>0.5
LED Chip Type	:	SMD-Samsung Chip
CRI	:	>80
Certification	:	EMC,LVD,ROHS
IP Rating Protection Class	:	IP20
Body type	:	ABS+Plastic
Dimmable	:	No
Life Time	:	30,000 Hours
EAN code	:	3800157630627
Unit size	:	120x37mm
Packing details	:	40.00

PRODUCT FEATURES

- Contemporary & Elegant Design
- Higher Light Transmission Rate
- No flickering, No U.V Radiation
- No Lead or Mercury content hence Environment friendly
- Suitable for office and general lighting (Conference Room, Showroom, lobby, cabin, kitchen etc.)
- High quality power driver
- Instant light 100% O s
- Temp -20 to + 45°C