

LED Panel Series



VT-620RD

HIGHLIGHTS :

WATTS



20

EQ. WATTS



120

LUMINOUS



2000

BEAM ANGLE



120

| | | |
|----------------------------|---|------------------|
| Item No | : | VT-620RD |
| SKU Code | : | 614 |
| Watts | : | 20 |
| Voltage | : | AC:220-240V,50Hz |
| Lumen(lm) | : | 2000 |
| Color Temperature | : | 3000K |
| Beam Angle | : | 120 |
| Commercial type | : | Round |
| PF | : | >0.9 |
| LED Chip Type | : | SMD-Samsung Chip |
| CRI | : | >80 |
| Certification | : | EMC,LVD,ROHS |
| IP Rating Protection Class | : | IP20 |
| Body type | : | ABS+Plastic |
| Dimmable | : | No |
| Life Time | : | 30,000 Hours |
| EAN code | : | 3800157630559 |
| Unit size | : | 170x37mm |
| Packing details | : | 40.00 |

PRODUCT FEATURES

- Contemporary & Elegant Design
- Higher Light Transmission Rate
- No flickering, No U.V Radiation
- No Lead or Mercury content hence Environment friendly
- Suitable for office and general lighting (Conference Room, Showroom, lobby, cabin, kitchen etc.)
- High quality power driver
- Instant light 100% O s
- Temp -20 to + 45°C