

## LED Bulb Series



VT-230

### HIGHLIGHTS :

WATTS



11

EQ. WATTS



95

LUMINOUS



825

BEAM ANGLE



40

### PRODUCT FEATURES

Item No	:	VT-230
SKU Code	:	153
Watts	:	11
EQ. Watts	:	95
Base / holder	:	E27
Voltage	:	AC:220-240V,50Hz
Lumen(lm)	:	825
Color Temperature	:	3000K
Beam Angle	:	40
Commercial type	:	PAR30
PF	:	>0.5
LED Chip Type	:	SMD-Samsung Chip
CRI	:	>80
Energy rating label	:	A+
Certification	:	EMC,LVD,ROHS
IP Rating Protection Class	:	IP20
Body type	:	Thermoplastic
Dimmable	:	No
Life Time	:	30,000 Hours
Operation Temperature	:	-25 to +45°C
EAN code	:	3800157627665
Unit size	:	ø95x117mm
Packing details	:	30.00
Unit cbm	:	0.00140