

LED Bulb Series



VT-238

HIGHLIGHTS :

WATTS



14

EQ. WATTS



120

LUMINOUS



1100

BEAM ANGLE



40

PRODUCT FEATURES

Item No	:	VT-238
SKU Code	:	151
Watts	:	14
EQ. Watts	:	120
Base / holder	:	E27
Voltage	:	AC:220-240V,50Hz
Lumen(lm)	:	1100
Color Temperature	:	4000K
Beam Angle	:	40
Commercial type	:	PAR38
PF	:	>0.5
LED Chip Type	:	SMD-Samsung Chip
CRI	:	>80
Energy rating label	:	A+
Certification	:	EMC,LVD,ROHS
IP Rating Protection Class	:	IP20
Body type	:	Thermoplastic
Dimmable	:	No
Life Time	:	30,000 Hours
EAN code	:	3800157627641
Unit size	:	ø120x132mm
Packing details	:	30.00