

LED Bulb Series



VT-240

HIGHLIGHTS :

WATTS



40

EQ. WATTS



LUMINOUS



3500

BEAM ANGLE



120

PRODUCT FEATURES

Item No	:	VT-240
SKU Code	:	284
Watts	:	40
Base / holder	:	E27
Voltage	:	AC:220-240V,50Hz
Lumen(lm)	:	3500
Color Temperature	:	4000K
Beam Angle	:	120
PF	:	>0.9
LED Chip Type	:	SMD-Samsung Chip
CRI	:	>80
Certification	:	EMC,LVD,ROHS
IP Rating Protection Class	:	IP20
Body type	:	Aluminum
Dimmable	:	No
Life Time	:	30,000 Hours
EAN code	:	3800157634342
Unit size	:	90x212mm
Packing details	:	20.00