

## LED Spotlights



VT-247D

### HIGHLIGHTS :

WATTS



6.5

EQ. WATTS



55

LUMINOUS



450

BEAM ANGLE



110

### PRODUCT FEATURES

|                            |   |                  |
|----------------------------|---|------------------|
| Item No                    | : | VT-247D          |
| SKU Code                   | : | 198              |
| Watts                      | : | 6.5              |
| EQ. Watts                  | : | 55               |
| Base / holder              | : | GU10             |
| Voltage                    | : | AC:220-240V,50Hz |
| Lumen(lm)                  | : | 450              |
| Color Temperature          | : | 3000K            |
| Beam Angle                 | : | 110              |
| PF                         | : | >0.5             |
| LED Chip Type              | : | SMD-Samsung Chip |
| CRI                        | : | >80              |
| Energy rating label        | : | A+               |
| IP Rating Protection Class | : | IP20             |
| Body type                  | : | Plastic          |
| Dimmable                   | : | Yes              |
| Life Time                  | : | 30,000 Hours     |
| EAN code                   | : | 3800157631631    |
| Unit size                  | : | ø50x55mm         |
| Packing details            | : | 200.00           |