

LED Candle Series



VT-254D

HIGHLIGHTS :

WATTS



4

EQ. WATTS



30

LUMINOUS



350

BEAM ANGLE



300

PRODUCT FEATURES

Item No	:	VT-254D
SKU Code	:	278
Watts	:	4
EQ. Watts	:	30
Base / holder	:	E14
Voltage	:	AC:220-240V,50Hz
Lumen(lm)	:	350
Color Temperature	:	2700K
Beam Angle	:	300
Commercial type	:	C37
PF	:	>0.5
LED Chip Type	:	Filament-Samsung Chip
CRI	:	>80
Energy rating label	:	A+
IP Rating Protection Class	:	IP20
Body type	:	Glass
Dimmable	:	Yes
Life Time	:	20,000 Hours
EAN code	:	3800157634250
Unit size	:	ø35x100mm
Packing details	:	100.00