

LED Filament Series



VT-286

HIGHLIGHTS :

WATTS



6

EQ. WATTS



60

LUMINOUS



806

BEAM ANGLE



300

PRODUCT FEATURES

Item No	:	VT-286
SKU Code	:	294
Watts	:	6
EQ. Watts	:	60
Base / holder	:	E27
Voltage	:	AC:220-240V,50Hz
Lumen(lm)	:	806
Color Temperature	:	2700K
Beam Angle	:	300
Commercial type	:	G95
PF	:	>0.5
LED Chip Type	:	Filament-Samsung Chip
CRI	:	>80
Energy rating label	:	A++
Certification	:	CE,EMC,ROHS
IP Rating Protection Class	:	IP20
Body type	:	Glass
Dimmable	:	No
Life Time	:	20,000 Hours
Operation Temperature	:	-25 to +50°C
EAN code	:	3800157634724
Unit size	:	95x135mm
Packing details	:	20.00