


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0934441501](#)  
**Status:** **Active**  
**Overview:** [ML-XT Sealed Connection System](#)  
**Description:** ML-XT Sealed 2 Circuit Receptacle Housing with Heatshrink, Pre-Assembled with Small Rear Seal and Cover, Black

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification 934430002-K (PDF)</a>
<a href="#">Product Specification 934430010-P (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification STR-1707-001 (PDF)</a>	<a href="#">Product Literature (PDF)</a>
<a href="#">Application Specification 934430010-A (PDF)</a>	



*Series image - Reference only*

**Agency Certification**

UL E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">93444</a>
Application	Power, Signal, Wire-to-Wire
Application Tooling Part Link	63824-5300
Overview	<a href="#">ML-XT Sealed Connection System</a>
Product Literature Order No	987651-0201
Product Name	ML-XT
UPC	889056414739

**Physical**

Circuits (maximum)	2
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	6.367/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55°C to +125°C

**Electrical**

Current - Maximum per Contact 13.0A

**Material Info**

**Reference - Drawing Numbers**

Application Specification	934430010-A
Packaging Specification	934430002-K
Product Specification	934430010-P, STR-1707-001
Sales Drawing	934430010-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2018 (15  
January 2018)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[93444 Series](#)

**Mates With**

ML-XT Sealed 2 Circuit Plug Housing  
[93445-1501](#)

**Use With**

ML-XT Male (Pin) Terminal [84524-0004](#) (Nickel), ML-XT Male (Pin) Terminal [84524-0014](#) (Selective Gold), ML-XT 2 Circuit Receptacle Wedgelock [93447](#), ML-XT Blind Cavity Plug [93494-1000](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extraction Tool  
for ML-XT Sealed  
Connection System  
and Crimp Terminals

0638245300

This document was generated on 05/03/2018

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**