




MEACO LOW ENERGY Dehumidifiers

MEACO PLATINUM RANGE



INDEPENDENT TEST RESULTS		
ANNUAL ENERGY CONSUMPTION (kWh)	113.2	VERY LOW
MEASURED DEHUMIDIFYING CAPACITY (LITRES/24H)	11.71	VERY GOOD
MEASURED ENERGY FACTOR (LITRES/kWh)	1.94	EXCELLENT
ENERGY EFFICIENCY GRADE	1	HIGHEST POSSIBLE RATING

INDEPENDENT TEST RESULTS		
ANNUAL ENERGY CONSUMPTION (kWh)	69.8	VERY LOW
MEASURED DEHUMIDIFYING CAPACITY (LITRES/24H)	6.216	VERY GOOD
MEASURED ENERGY FACTOR (LITRES/kWh)	1.67	EXCELLENT
ENERGY EFFICIENCY GRADE	1	HIGHEST POSSIBLE RATING



SUPERIOR QUALITY = CHEAPER RUNNING COSTS




The new Platinum range of dehumidifiers from Meaco creates a new benchmark for domestic dehumidifiers by lowering consumers running costs and increasing build quality to a level that can **save customers over £100 per year on their electricity bill.***


There are two new models in the Platinum range – the Meaco 12L Low Energy Dehumidifier and the Meaco 20L Low Energy Dehumidifier, the 12 litre model sets a new standard drawing just 165 watts while the 20 litre is even more remarkable at just 255 watts (some dehumidifiers use twice this level).

These low consumption figures will save you a huge amount of money in electricity charges year in year out. In order to create a dehumidifier that performs and runs so efficiently we had to not only optimise the design but every individual component had to be of the highest quality. This results in a dehumidifier that is quieter, stronger and more robust than other dehumidifiers on the market. These new Meaco dehumidifiers really do stand out in a class of their own which is why we have classified them as being our first Platinum dehumidifiers.

12L unit




20L unit



EACH MODEL HAS A RICH SET OF FEATURES INCLUDING

	Meaco 12L Low Energy Dehumidifier	Meaco 20L Low Energy Dehumidifier
Dehumidifying capacity	12L (30°C 80%rh) 6.2L (26.7°C 60%rh)	20L (30°C 80%rh) 11.71L (26.7°C 60%rh)
Meaco unique control logic	✓	✓
Digital display	✓	✓
Rated power	165 watts	255 watts
Auto re-start	✓	✓
Filter	Dust filter with optional HEPA filter	
Electronic variable humidistat	✓	✓
Louvre	Yes - Manual	Yes - Electronic rotating
Air volume	100m ³ /h	160m ³ /h
Maximum noise level	44dB(A)	46dB(A)
Timer	1~24h	1~24h
Child lock	✓	✓
Fan Speed	1	2
Water tank capacity	2.5L	6L
Operating temperature	5°C~35°C	5°C~35°C
Net weight	9.5 kg	12.6 kg
Product Size (WxDxH)	325 x 248 x 485mm	385 x 290 x 595mm



Should you be concerned about not just dealing with damp air but you also wish to achieve clean air then you can add a HEPA filter to your Platinum dehumidifier to remove pollutants smaller than the eye can see.

By buying and using a Meaco Platinum range dehumidifier you are not only investing in a dehumidifier that will combat mould, condensation and damp problems, you are also buying a high end, quality piece of engineering, that has been tested against the highest international standards.

Meaco (U.K.) Limited, Meaco House, Parklands, Railton Road, Guildford, Surrey, GU2 9JX
t : 01483 234900 e : sales@meaco.com

www.meaco.com

*electricity savings based on data taken from Energy Saving Trust website and manufacturer's and reseller's websites October 2013.