


# CAMBLOCK

## 5mm Pitch Pluggable Terminal Blocks for Vertical or 90° Mounting

- 2 & 3 pole interlocking
- Moulded in black UL94-V0 PA66 flame retardant PA66
- Wire protector terminals
- Captive screws
- 0.33-2mm<sup>2</sup> (22-14AWG)
- Guided pin alignment
-  approved


CTB1302



### SPECIFICATION


Rating	10A 250V
Insulation resistance	5000M Ω/1000V
Withstand voltage	AC1500V/1min
Contact resistance	20m Ω
Working temperature	-33°C to +120°C
Mouldings	UL94-V0 flame retardant PA66
Terminal	Tin plated brass
Wire protector	Tin plated copper
Screw/torque	M2.5 steel, nickel plated 0.4Nm

TYPE NO.	POLES	LENGTH
CTB1302/2	2	10mm
CTB1302/3	3	15mm
CTB1302/4	4	20mm
CTB1302/5	5	25mm
CTB1302/6	6	30mm
CTB1302/7	7	35mm
CTB1302/8	8	40mm
CTB1302/9	9	45mm
CTB1302/10	10	50mm
CTB1302/11	11	55mm
CTB1302/12	12	60mm



PCB  
TERMINAL  
BLOCKS

## 5mm Pitch 24 Pin Strip Header

- Supplied in 24-way strips
- Easily cut to required length
- Can be supplied pre-cut
- Moulded in UL94-V0 flame retardant PA66
- 0.33-2mm<sup>2</sup> (22-14AWG)
- Anti solder wicking pins
- Guided pin alignment
-  approved


CTB1302/PS



### SPECIFICATION

Rating	10A 250V
Insulation resistance	5000M Ω/1000V
Withstand Voltage	AC1500V/1min
Contact Resistance	20m Ω
Working Temperature	-33°C to +120°C
Mouldings	UL94-V0 flame retardant PA66
Pin	Stainless steel
Recommended PCB hole size	ø1.6mm

TYPE NO.	POLES	DESCRIPTION
CTB1302/PS24	24	24-Way Pin Strip



+44 (0)1638 716101  
info@camdenboss.com  
www.camdenboss.com

We operate a constant improvement policy, our products are subject to change without notice.

Ver 1

**CAMDENBOSS**  
ELECTRONICS & ENCLOSURES