



2W

VT-202 2W ST26 PLASTIC BULB WITH SAMSUNG CHIP
 COLORCODE:3000K

Equivalent 20W	Lumens 180	Beam Angle 150	Dimensions 25x59mm
--------------------------	----------------------	--------------------------	------------------------------

Warm White
 SKU:234



5 YEARS
 WARRANTY



Technical Information

Instant Start: No	Energy Rating: A+
EQ-WATTS: 20	Long life: 30,000 Hours
Watts: 2	LED Chip Type: SMD
Lumens: 180	IP Rating: IP20
Holder Type: E14	Dimmable: No
Shape: ST26	Warranty (Years): 5
Beam Angle: 150	PF: >0.4
Unit Color: White	CRI: >80
Body Type: Thermoplastic	Input Power: AC:220-240V,50Hz



Features

- ✓ LED Bulbs are the best replacement for conventional Incandescent or Fluorescent Bulbs
- ✓ Stable SMD technology which makes the product more reliable and durable
- ✓ Highly Efficient LED Samsung Chip
- ✓ Constant current Integrated IC driver
- ✓ High endurance and Durability
- ✓ Excellent Heat Radiation Efficiency
- ✓ High luminous efficacy & Low Power consumption
- ✓ No Flickering - No UV Radiation - No Mercury
- ✓ Complies with LM-80
- ✓ Application - Residential Lighting, Commercial Lighting, Decorative, Living Room, Lounge etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.015162
Unit CBM	0.000062

Listing Details

EAN Code	3800157632546
----------	---------------

Master Box Packaging

Master Box Qty (Pcs Per Carton)	400
---------------------------------	-----

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES