

LED Bulb Series



VT-202

HIGHLIGHTS :

WATTS



2

EQ. WATTS



20

LUMINOUS



180

BEAM ANGLE



150

PRODUCT FEATURES

| | | |
|----------------------------|---|------------------|
| Item No | : | VT-202 |
| SKU Code | : | 235 |
| Watts | : | 2 |
| EQ. Watts | : | 20 |
| Base / holder | : | E14 |
| Voltage | : | AC:220-240V,50Hz |
| Lumen(lm) | : | 180 |
| Color Temperature | : | 4000K |
| Beam Angle | : | 150 |
| Commercial type | : | ST26 |
| PF | : | >0.4 |
| LED Chip Type | : | SMD-Samsung Chip |
| CRI | : | >80 |
| Energy rating label | : | A+ |
| IP Rating Protection Class | : | IP20 |
| Body type | : | Thermoplastic |
| Dimmable | : | No |
| Life Time | : | 30,000 Hours |
| EAN code | : | 3800157632553 |
| Unit size | : | ø25x59mm |
| Packing details | : | 400.00 |