

LED Bulb Series



VT-212

HIGHLIGHTS :

WATTS



11

EQ. WATTS



75

LUMINOUS



1055

BEAM ANGLE



200

PRODUCT FEATURES

Item No	:	VT-212
SKU Code	:	232
Watts	:	11
EQ. Watts	:	75
Base / holder	:	E27
Voltage	:	AC:220-240V,50Hz
Lumen(lm)	:	1055
Color Temperature	:	4000K
Beam Angle	:	200
Commercial type	:	A58
PF	:	>0.5
LED Chip Type	:	SMD-Samsung Chip
CRI	:	>80
Energy rating label	:	A+
IP Rating Protection Class	:	IP20
Body type	:	Thermoplastic
Dimmable	:	No
Life Time	:	30,000 Hours
EAN code	:	3800157631976
Unit size	:	ø60x106mm
Packing details	:	100.00