

## LED Bulb Series



### VT-224

#### HIGHLIGHTS :

WATTS



24

EQ. WATTS



120

LUMINOUS



1900

BEAM ANGLE



120

#### PRODUCT FEATURES

|                            |   |                  |
|----------------------------|---|------------------|
| Item No                    | : | VT-224           |
| SKU Code                   | : | 216              |
| Watts                      | : | 24               |
| EQ. Watts                  | : | 120              |
| Base / holder              | : | E27              |
| Voltage                    | : | AC:220-240V,50Hz |
| Lumen(lm)                  | : | 1900             |
| Color Temperature          | : | 3000K            |
| Beam Angle                 | : | 120              |
| Commercial type            | : | F200             |
| PF                         | : | >0.5             |
| LED Chip Type              | : | SMD-Samsung Chip |
| CRI                        | : | >80              |
| Energy rating label        | : | A+               |
| IP Rating Protection Class | : | IP20             |
| Body type                  | : | Thermoplastic    |
| Dimmable                   | : | No               |
| Life Time                  | : | 30,000 Hours     |
| EAN code                   | : | 3800157631815    |
| Unit size                  | : | 200x80mm         |
| Packing details            | : | 20.00            |