

LED Bulb Series



VT-224

HIGHLIGHTS :

WATTS



24

EQ. WATTS



120

LUMINOUS



1900

BEAM ANGLE



120

PRODUCT FEATURES

Item No	:	VT-224
SKU Code	:	218
Watts	:	24
EQ. Watts	:	120
Base / holder	:	E27
Voltage	:	AC:220-240V,50Hz
Lumen(lm)	:	1900
Color Temperature	:	6400K
Beam Angle	:	120
Commercial type	:	F200
PF	:	>0.5
LED Chip Type	:	SMD-Samsung Chip
CRI	:	>80
Energy rating label	:	A+
IP Rating Protection Class	:	IP20
Body type	:	Thermoplastic
Dimmable	:	No
Life Time	:	30,000 Hours
EAN code	:	3800157631839
Unit size	:	ø200x80mm
Packing details	:	20.00